







ROHS
Compatible




SECTION A-A
SCALE 1:1



SECTION B-B
SCALE 1:1

U5	214-	24P	x	XXB	XXL
名称	流水号	PIN位	N;母座	B;夹板	L;长度
				0.8	8.8
				1.0	9.3
					10.0
					10.5



长度可选规格如下


4	10.5
3	10.0
2	9.3
1	8.8
NO	DIM A

DESIGN	LI Jinwei	SCALL			DRAWG NO. U5214-24PNXXBXXL
DRAWING	Wu Qifa	UNIT	mm		
CHECK	Zheng Jinxian	SIZE	A4: 210 * 297		
APPROVAL	Liu Xiaohong	DATE	2020-06-10		
				TOLERANCE	TITLE: 24P 夹板
				X.X ±0.30 X.°±2°	
				.XX ±0.20 .X°±1°	
				.XXX ±0.10 .XX°±0.5°	



广东宏煜盛电子科技有限公司
Guangdong Hongyusheng Electronic Technology Co., Ltd.
TEL:0752-6632356 <https://www.hystypec.com>

ROHS
Compatible



RECOMMENDED P.C.B. LAYOUT (T:1.00mm)

TOLERANCE UNSPECIFIED $\pm 0.05\text{mm}$

USB TYPE-C FULL-FEATURED RECEPTACLE INTERFACE PIN ASSIGNMENTS

	A	B
1	GND	12 GND
2	SSTXp1	11 SSRXp1
3	SSTXn1	10 SSRXn1
4	VBUS	9 VBUS
5	CC1	8 SBU2
6	Dp1	7 Dn2
7	Dn1	6 Dp2
8	SBU1	5 CC2
9	VBUS	4 VBUS
10	SSRXn2	3 SSTXn2
11	SSRXp2	2 SSTXp2
12	GND	1 GND

特性:

一、电气性能: ELECTRICAL

1. 额定电流: 5A
2. 接触阻抗: 40 MILLIOHMS MAX
3. 耐电压: 150V AC / 1 mA MAX
4. 绝缘阻抗: 150V DC/100 MEGA OHMS MIN

二、机械性能:

1. 插入力: 5~20N
2. 拔出力: 8~20N
3. 使用寿命: 10000次、拔出力 6~20N

三、材料: MATERIAL

1. 塑胶: LCP E130I 黑色 UL94V-0
2. 端子: C2680/C7025 T=0.15MM
3. 外壳: SUS304 T=0.30MM
4. 接地片: SUS304 T=0.10MM
5. 卡勾: SUS301 T=0.15MM

四、电镀: FINISH

1. 端子: 接触点镀金3U"MIN
PIN脚焊接区域雾锡60U"MIN.
2. 外壳: 镀镍50U"MIN

五、电镀品需做粘锡测试: 粘锡面积达到95%以上。

六、SMT回流焊 (峰值 $265^{\circ}\text{C} \pm 5^{\circ}\text{C}$) 不能起泡、
熔胶、变色不良 (变形在公差范围以内)

七、工作温度: $-55^{\circ}\text{C} \sim +85^{\circ}\text{C}$


八、盐雾测试: 通过48H在浓度为 $5 \pm 1\%$ 盐水的盐雾测试无生锈
现象

DESIGN	LI Jinwei	SCALL		 TOLERANCE X.X ±0.30 X.°±2° .XX ±0.20 .X.° ±1° .XXX ±0.10 .XX°±0.5°	DRAWG NO. U5214-24PNXXBXXL	 广东宏煜盛电子科技有限公司 Guangdong Hongyusheng Electronic Technology Co., Ltd TEL:0752-6632356 https://www.hystypec.com
DRAWING	Wu Qifa	UNIT	mm		TITLE: 24P 夹板	
CHECK	Zheng Jinxian	SIZE	A4: 210 * 297			
APPROVAL	Liu Xiaohong	DATE	2020-06-10			

ROHS
Compatible

將成品依同一方向放入真空盤內, 如圖所示。

At same direction, put product onto the tray. Direction refers to below drawing.



VIEW-1

二.

1) 一只紙箱可放置之包裝盤(包括上蓋)見下表。


1) trays per carton, please see next table.

2). 每1個紙箱用的包裝數量詳見下表。

2) The Q'ty of products per carton please see next table.

3) 將裝滿成品的真空盤用 PE帶捆緊後放在塑膠袋內, 裝完後再封箱。

3) Bind the trays with PE tape and then, put them into the poly bag. Seal the carton with tape.




VIEW-2

三.

1). 將標籤貼於紙箱側麥上方。

Stick the needful label On the up-right corner of the side of carton.



VIEW-3

備 註(REMARK)

1. 若有未裝滿之零數箱, 必須以緩衝材塞滿。

The unfilling-carton must be filled with assuagement.

2. 防水袋需用膠帶貼實且封口。

waterproof plastic bag must be folded up.

3. 裝滿成品后之外箱, 最大堆積箱數: 5箱

About the box fully filled with products, the MAX accumulating quantity of boxes is 5.

4. 如須貼Bar-code, 請依Bar-code作業辦法執行

If barcode lable is required, do it according to

the related barcode lable operation standards.

DESIGN	LI Jinwei	SCALL			DRAWG NO.	U5214-24PNXXBXXL
DRAWING	Wu Qifa	UNIT	mm	TOLERANCE		
CHECK	Zheng Jinxian	SIZE	A4: 210 * 297	X.X ±0.30 X.° ±2°	TITLE:	24P 夹板
APPROVAL	Liu Xiaohong	DATE	2020-06-10	.XX ±0.20 .X° ±1°		
				.XXX ±0.10 .XX° ±0.5°		



广东宏煜盛电子科技有限公司

Guangdong Hongyusheng Electronic Technology Co., Ltd.

TEL: 0752-6632356 <https://www.hystypec.com>